

Features

- Includes tamper resistant locking nut to prevent accidental misadjustment
- Built-in check valves prevent migration of hot water to cold and cold water to hot water piping
- Provided with cap for three port application
- Integral strainer with 40 mesh stainless steel screens to filter

Material

- Lead Free* Brass body construction

Installation

- Installs easily between the stop valves and faucet




Codes/Standards

ASSE 1070
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
IAPMO Certification

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: No

Spout:

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation guide.