

Features

- Sleek contemporary design
- Single joystick handle allows for both volume and temperature control
- Red/blue indexing
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- 5.69 inch (144 mm) spout reach
- 3.5 inch (89 mm) spout height
- 2.12 gpm (8.0 lpm) maximum faucet flow rate at 43.51 psi (3.0 bar)
- Includes clicker drain with 1.25 inch (32 mm) metal tailpiece
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability

Installation

- Deck-mount
- Single-hole installation



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Drain included: No

Drain with overflow: No

Notes

Install this product according to the installation guide.