

KOHLER® Faucets

Round 203 mm single-function rainhead, 12.1 lpm
K-99945T-CL

Features

- Single-function round rainhead features Full Coverage with Katalyst™ air-induction technology, a drenching spray experience ideal for rinsing shampoo from hair
- Angled nozzles provide a full-coverage spray
- 3.2 gpm (12.1 lpm) maximum flow rate at 45 psi (3.1 bar)

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall- or ceiling-mount
- G 1/2 inlet connection
- Requires rainhead arm and flange (sold separately)

Recommended Products/Accessories



K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB/T 23447

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: No

Showerhead/Body Spray:

Rated maximum flow: 3.17 gal/min (12 l/min)