

### Features

- Set includes: Cabinet, precut Silestone® quartz vanity top, sinks, cabinet hardware, mounting hardware for sinks
- Vanity top has single faucet hole with pilot holes for optional 8" (203 mm) widespread faucet configuration at each sink location
- Full-extension 18" (457 mm) depth drawers with soft-close undermount slides for smooth opening
- Solid wood drawers with dovetail joint construction
- Vanity top is covered under the Silestone® 25-Year Limited Warranty
- Silestone® quartz provides exceptional durability and stain resistance, making it easy to maintain
- Caxton® Rectangle undermount sink has a streamlined design that is easy to clean
- Customize your storage with optional in-drawer accessories, medicine cabinet surrounds and side kits (sold separately)
- Optional vanity top side and backsplashes available (sold separately)

### Material

- Solid and composite wood
- Silestone® quartz vanity top
- Vitreous china sink
- Premium metal hardware for durability and reliability

### Installation

- Wall-hung

### Required Products/Accessories

- K-27938 60" vanity legs
- K-28265 Silestone® quartz 61" backsplash (Qty 2)

### Included Components

- K-33565 17" cabinet pull (Qty 2)
- K-EC20000 20-1/2" rectangular undermount bathroom sink (Qty 2)
- K-33563 60" wall-hung bathroom vanity cabinet
- K-28258 Silestone® 61" quartz vanity top with two rectangular cutouts



### Codes/Standards

EPA TSCA Title VI/CARB P2



### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes


*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	White
	GL7	Gloss Black



**Enivo®**  
60" wall-hung bathroom vanity cabinet with sinks and  
quartz top  
**K-CM33563-BD1**



**Technical Information**

All product dimensions are nominal.

**Notes**

Install this product according to the installation instructions.