



Brazn™
Two-piece round-front toilet with skirted trapway,
dual-flush
K-EX22384T-SL

Features

- Two-piece design
- Round-front bowl offers an ideal solution for smaller bathrooms and powder rooms
- Skirted trapway simplifies cleaning
- French Curve™ Quiet-Close™ seat closes quietly and quickly unlatches from the toilet for easy removal and convenient cleaning
- Revolution 360™ flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Beveled rim slants toward interior of bowl so excess liquid does not accumulate
- Includes left-hand Polished Chrome dual-flush trip lever
- 1.28 gpf (4.8 lpf) or 0.8 gpf (3.0 lpf)
- 1-7/8" (48 mm) fully glazed trapway
- Combination consists of K-EX22386T-0 bowl, K-EX22382T-ST4-0 tank, and K-EX22380T-0 seat

Material

- Vitreous china

Installation


- 15-3/4" (400 mm) rough-in
- Floor-mount



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round-front
Flush type:	Revolution 360, AquaPiston
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6" (152 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.