

KOHLER® Faucets

Widespread bathroom sink faucet with handles and spout

Occasion™
K-EX27101T-9

Features

- Two knob handles offer separate control of hot and cold water
- 6" (152 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow
- Includes cable pop-up drain with 1-1/4" (32 mm) tailpiece
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Part of the Occasion bathroom faucet and accessory collection

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- For 8" – 16" (203 – 406 mm) centers
- Deck-mount

Required Products/Accessories

K-27010-3 Cross bathroom sink faucet handles

or


K-27010-4 Lever bathroom sink faucet handles

or

K-27010-9 Knob bathroom sink faucet handles

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain with overflow: No

Notes

Install this product according to the installation guide.