

Features

- Stationary spout
- 7-1/2" (191 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Coordinate with your choice of Components™ bathroom sink faucet handles for a personalized design

Material

- Brass
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Mounts on finished wall surface
- Trim only; requires valve to complete installation (sold separately)

Required Products/Accessories

K-77980-4 Wall-mount bathroom sink faucet handle

or

K-77980-4A Wall-mount bathroom sink faucet handle

or

K-T77981-4 Wall-mount bathroom sink faucet Lever handle trim

or

K-T77981-8 Wall-mount bathroom sink faucet Oyl handle trim

or


K-T77981-9 Wall-mount bathroom sink faucet Industrial handle trim

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner
K-78372 18" Towel Bar
K-78373 24" Towel Bar
K-78375 24" Double Towel Bar
K-78377 Hand Towel Arm
K-78378 Robe Hook
K-78379 Double Towel Arm
K-78382 Pivoting toilet paper holder
K-78383 Vertical toilet paper holder
K-78384 Covered double toilet paper holder


Optional Products/Accessories

K-7107 Decorative Drain
K-7108 Decorative Drain
K-7114 Pop-Up Drain
K-7127 Drain
K-7129 Drain
K-33151 Clicker drain without overflow

**Codes/Standards**

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: Yes

Drain with overflow: No

Spout:

Spout reach: $7\text{-}1/2\text{''}$ (191 mm)

Notes

Install this product according to the installation instructions.