

### Features

- Stationary spout
- 7-11/16" (195 mm) spout reach
- 2.2 gpm (8.3 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Coordinate with your choice of Components™ bathroom sink faucet handles for a personalized design

### Material

- Brass
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Mounts on finished wall surface
- Trim only; requires valve to complete installation (sold separately)

### Required Products/Accessories

K-77980-4 Wall-mount bathroom sink faucet handle

or

K-77980-4A Wall-mount bathroom sink faucet handle

or

K-T77981-4 Wall-mount bathroom sink faucet Lever handle trim

or

K-T77981-8 Wall-mount bathroom sink faucet Oyl handle trim

or


K-T77981-9 Wall-mount bathroom sink faucet Industrial handle trim

### Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner  
K-78372 18" Towel Bar  
K-78373 24" Towel Bar  
K-78375 24" Double Towel Bar  
K-78377 Hand Towel Arm  
K-78378 Robe Hook  
K-78379 Double Towel Arm  
K-78382 Pivoting toilet paper holder  
K-78383 Vertical toilet paper holder  
K-78384 Covered double toilet paper holder

### Optional Products/Accessories


K-7107 Decorative Drain  
K-7108 Decorative Drain  
K-7114 Pop-Up Drain  
K-7127 Drain  
K-7129 Drain  
K-33151 Clicker drain without overflow



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

Drain included: Yes

Drain with overflow: No

**Notes**

Install this product according to the installation instructions.