

Features

- Kinesis™ technology with concealed sensor allows for a clean aesthetic and provides extraordinarily accurate and reliable actuation in varying installation environments
- On-demand usage with 60-second max. continual run cycle to prevent vandalism and save water
- Design-forward aesthetic for commercial bathroom spaces
- Long reach is ideal for larger sinks
- Vandal-resistant aerator
- 9-3/5" (245 mm) spout reach
- 13-3/8" (340 mm) stainless steel supply tube
- Aerated flow delivers a smooth, steady stream of water
- For use with cold water line only
- 0.26 gpm (1.0 lpm) maximum flow rate
- Below-counter valving reduces the faucet footprint and provides easier service
- Grid drain with tailpiece
- Includes spout assembly, control box assembly, supply tube, aerator key, and standard installation hardware
- Concealed mechanical mixer sold separately
- Wall-mount installation

Material


- Brass spout
- Durable plastic valve with brass connection

Technology

- Kinesis™ sensor technology offers on-demand detection for maximum water savings

Installation

- Requires AC or DC power unit (sold separately)


**Codes/Standards**

Plumbing Standards
CJ/T 164

See website for detailed warranty information.

KOHLER® Faucets

Components™
Touchless wall-mount 245 mm lavatory faucet with
Kinesis™ sensor technology, 1.0 lpm
K-EX39561T-NWS5



Technical Information

All product dimensions are nominal.

Drain included: Yes

Drain with overflow: No

Notes

Install this product according to the installation guide.