

# Highcliff™ Ultra

### Antimicrobial toilet with Mach® Tripoint® flushometer K-PR96057-T5DS

### **Features**

- Fixture and touchless flushometer combination is engineered for optimal performance
- Elongated bowl offers added room and comfort
- Antimicrobial finish inhibits the growth of mold-, mildew-, stain-, and odor-causing bacteria on the fixture surface. This product does not protect users against bacteria, viruses, or other disease organisms. Always clean and wash this product thoroughly before and after each use
- 2-1/8" (54 mm) fully glazed trapway
- 10" x 7" (254 mm x 178 mm) water surface
- 10" or 12" (254 or 305 mm) rough-in
- 1.6 gpf (6.0 lpf)
- Flush valve activation distance is factory-set
- No external flush volume adjustment ensures water conservation
- 24-hour automatic sentinel flush keeps trapway fresh
- Mechanical override enables flushometer to be used manually even during a power outage
- Chloramine and chlorine resistance on all rubber components DOE Energy Policy Act 1992 exposed to waterway
- Locking stop cap provides protection against vandalism
- Powered by 1.5V AA lithium batteries
- For this combination, order K-96057-SS bowl and K-10TD00R10 flushometer

#### Material

- Vitreous china bowl
- Brass flush valve with durable Polished Chrome finish

### Technology

- Electronic infrared sensor with Tripoint® technology for accurate activation
- Designed to outperform competitors in bowl cleanliness and plug resistance

### Installation

Seat sold separately



ADA CSA B651 OBC

### Codes/Standards

IAPMO Certification

ASME A112.18.1/CSA B125.1 ASME A112.19.2/CSA B45.1 ASSE 1037/ASME A112.1037/CSA B125.37 DOE - Energy Policy Act 1992 ADA ICC/ANSI A117.1 CSA B651 OBC

# **KOHLER® One-Year Limited Warranty**


See website for detailed warranty information.





# Highcliff™ Ultra

### Antimicrobial toilet with Mach® Tripoint® flushometer K-PR96057-T5DS



### **Technical Information**

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor Bowl shape: Elongated

Flush type: Flushometer valve siphon

Spud size: 1 1/2, Inlet, Top 2-1/8" (54 mm) Trap passageway:

Water surface size: 10" x 7" (254 mm x 178 mm)

Rim to water 6" (152 mm)

surface:

Rough-in: 12" (305 mm) 5-1/2" (140 mm) Seat-mounting

holes:

### **Fixture Supply Requirements**

35 psi (241.3 kPa) Max static pressure: 80 psi (551.6 kPa) Min flowing 25 psi (172.4 kPa)

pressure:

## Min static pressure:

### **Notes**

Install this product according to the installation

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

For ADA installations, rear grab bar may need to be split or shifted.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.

