



# Ridgeport™ | K-R30997-4D

Centerset bathroom sink faucet, 1.2 gpm

## Features

- Two-handle centerset faucet for 4" (102 mm) centers
- Two Lever handles offer separate control of hot and cold water
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- 1.2 gpm (4.5 lpm) maximum flow rate



1-800-4KOHLER (1-800-456-4537)  
Kohler Co. reserves the right to make revisions without notice to product specifications.  
For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
4-15-2026 5:29 - US-CA

THE BOLD LOOK  
OF **KOHLER**®

## Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

CSA B651 OBC

ASME A112.18.1/CSA B125.1  
 NSF/ANSI/CAN 372  
 NSF/ANSI/CAN 61  
 DOE - Energy Policy Act 1992  
 EPA WaterSense®  
 California Energy Commission (CEC)  
 NSF/ANSI/CAN 61|NSF/ANSI/CAN 372  
 ADA  
 ICC/ANSI A117.1  
 CSA B651  
 OBC

## Technical Information

All product dimensions are nominal.

### Handle

Handle Style/ Type: Lever

### Spout

Spout Reach: 4-13/16" (122 mm)

### Flow Rate

Faucet Flow Rate: 1.2 gpm (4.5 l/min)

## Recommended Products/Accessories

K-23726 Drain treatment


K-23723 Faucet cleaner

## Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty





## Installation

- Simplified faucet installation; mounting hardware requires no special tools
- Includes clicker drain

## Installation Notes

*Install this product according to the installation instructions.*

ADA compliant for handles only.  
 ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

