



Ealing® All-In-One

33" top-/undermount single-bowl kitchen sink
K-R39824-1PC

Features

- 36" (914 mm) minimum base cabinet width
- Single bowl
- 10-1/8" (257 mm) bowl depth
- Bowl slopes toward drain to minimize water pooling
- Rounded 3/8" (10 mm) corners are easy to clean
- Matte finish offers rich, dimensional color
- Semi-professional kitchen faucet with finish-matched easy-clean hose cover
- Two-function sprayhead with touch-control allows you to switch from aerated stream to Sweep® spray
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Box includes: Sink, assembled Vibrant Stainless semi-professional faucet, drain with strainer, cutout template, installation hardware



Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

Codes/Standards

ASME A112.18.1/CSA B125.1
CSA B45.5/IAPMO Z124
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
California Energy Commission (CEC)

KOHLER® Neoroc® Sinks Lifetime Limited Warranty KOHLER® Faucet Lifetime Limited Warranty KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Installation

- Top-mount or undermount
- Right drain
- Flexible supply lines and quick-connect fittings simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23730 Neoroc® cleaner

Optional Products/Accessories

K-11352 Disposal Flange with Stopper

Included Components

7400 Stainless Steel Sink Drain and Strainer
K-REC28702 Semi-professional kitchen sink faucet

Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	CM1	Matte Black
--	-----	-------------



Ealing® All-In-One
33" top-/undermount single-bowl kitchen sink
K-R39824-1PC



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 36" (914 mm)

Bowl area (Basin #1): Length: 30-1/8" (765 mm)
Width: 16-15/16" (430 mm)
Water depth: 9-1/2" (241 mm)

Number of deck holes: 1

Drain hole: 3-7/8" (98 mm)

Template: Top-mount/Undermount, 1281757-7,
required, included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1- 800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.