# Ealing® All-In-One | K-R39825-1PC

33" top-/undermount double-bowl kitchen sink

## Features

- 36" (914 mm) minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Single faucet hole
- Right rear drain placement increases workspace in the sink and storage space underneath
- Rounded 3/8" (10 mm) corners are easy to clean
- Matte finish offers rich, dimensional color
- Semi-professional kitchen faucet with finish-matched easy-clean hose cover
- Two-function sprayhead with touch-control allows you to switch from aerated stream to Sweep® spray
- High-arch spout offers vertical clearance for tall cookware and pitchers
- Box includes: Sink, assembled Vibrant® Stainless semi-professional faucet, two sink drains with strainers, cutout template, installation hardware

## Sustainability

## Available Colors/Finishes

***Color tiles intended for reference only.***

CM1 Matte Black



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 03:23 - US-CA

## Codes/Standards

ASME A112.18.1/CSA B125.1
CSA B45.5/IAPMO Z124
NSF/ANSI/CAN 372
NSF/ANSI/CAN 61
DOE - Energy Policy Act 1992
California Energy Commission (CEC)

## Technical Information

***All product dimensions are nominal.***

| | |
|---|---|
| Number of Deck Holes: | 1 |
| Faucet Hole(s) Size: | 1-7/16" (37 mm) |
| Drain Hole Diameter: | 3-7/8" (98 mm) |
| Minimum Base Cabinet Width: | 36" (914 mm) |
| Basin Configuration: | Equal Bowls |

## Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

## Included Components

- K-REC28702 Semi-professional kitchen sink faucet (QTY 1)

## Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket, less tailpiece
- [object Object]23726 Drain treatment
- K-23725 Cast iron cleaner
- K-5186 Stainless steel sink rack, 13 5/8" x 16 1/2", for right-hand bowl
- K-5662 Stainless steel sink rack, left-hand bowl
- K-11352 Disposal flange with stopper

## Warranty


***See website for detailed warranty information.***

KOHLER® Neoroc® Sinks Lifetime Limited Warranty|KOHLER® Faucet Lifetime Limited Warranty|KOHLER® One-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 03:23 - US-CA

THE BOLD LOOK OF KOHLER.




## Installation

- Top-mount or undermount
- Flexible supply lines and quick-connect fittings simplify installation

## Installation Notes

***Install this product according to the installation instructions.***

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1- 800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 03:23 - US-CA

THE BOLD LOOK OF KOHLER.