Rill® HydroRail® | K-R40336-G

Shower column kit, 1.75 gpm

Features

- Includes handshower, showerhead, 60" (1522 mm) shower hose, and slidebar
- Multifunction handshower features six sprays: full coverage, intense drenching, targeted massage, gentle mist, PowerSweep™, and TargetRinse™
- Full coverage spray produces an encompassing spray ideal for everyday use
- Intense rinse delivers a forceful spray ideal for thoroughly rinsing soap from hair
- Targeted massage to ease away aches and pains
- Gentle mist spray restores, with a thick cloud of silky, super-fine water droplets
- PowerSweep™ provides a concentrated jet of water to clean shower walls, remove caked-on mud from shoes and clothing, and is ideal for pets
- TargetRinse™ produces a controlled spray for deep cleaning
- Unique pivoting showerhead can also be applied as a rainhead
- Simple thumb tab smoothly transitions between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 1.75 gpm (6.6 lpm) maximum showerhead/handshower flow rate at 45 psi (3.1 bar)
- Slidebar bracket allows you to adjust height and angle of handshower
- Diverter at base of column makes for easy toggling between handshower and showerhead
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System



Sustainability

WATER-SAVING DESIGN

Available Colors/Finishes

Color tiles intended for reference only.

	CP	Polished Chrome
	BN	Vibrant Brushed Nickel
	BL	Matte Black
	2MB	Vibrant Brushed Moderne Brass

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-04-2026 21:00 - US-CA

THE BOLD LOOK OF KOHLER

Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

Technical Information

All product dimensions are nominal.

Flow Rate

Shower/Rainhead Rated Maximum Flow:	1.75 gpm (6.6 l/min)
Handshower Rated Maximum Flow:	1.75 gpm (6.6 l/min)

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing


Warranty

See website for detailed warranty information.

KOHLER® Faucet Lifetime Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-04-2026 21:00 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Wall-mount
- For use in shower-only installations
- Installs in less than 60 minutes without changes to in-wall plumbing (subject to condition of existing installation)
- May require additional service parts based on installation type (see installation guide for details)

Installation Notes

Install this product according to the installation instructions.

For use with automatic compensating valves rated at 1.4 gal/min (5.3 l/min) or less.
For use with showerheads or handsprays rated at 1.4 gal/min (5.3 l/min) or higher.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
11-04-2026 21:00 - US-CA

THE BOLD LOOK OF KOHLER