



Orime® | K-REC34051-SC03

Three-light sconce

Features

- Dome-shaped shade in clear glass combines with knurled metal for a contemporary and classic design
- Sconces can be positioned up or down, depending on room setting
- Medium base (E26) socket, three clear A19 LED bulbs included
- Suitable for damp locations, per UL 1598
- Includes installation hardware



Available Colors/Finishes

Color tiles intended for reference only.

- BNL Brushed Nickel
- CPL Polished Chrome
- BLL Matte Black
- 2GL Brushed Moderne Brass



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-09-2026 03:11 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA C22.2 No. 250.0

Technical Information

All product dimensions are nominal.

Number of Lights:	3
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	3
Hanging Type:	Non-hanging

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.

Lights: 120 V, 0.25 A, 60 Hz

Electrical Component Ratings


Socket Rating: 60 Hz, 9 W, 900 Lumens

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty





Installation Notes

Install this product according to the installation instructions.

