



Lyric® | K-RH20910

34" undermount single-bowl farmhouse kitchen sink

Features

- 36" minimum base cabinet width
- Single bowl
- 9" (229 mm) depth provides generous workspace
- With integral shortened Self-Trimming® apron
- The 7" (178 mm) short apron allows the sink to be used in most standard cabinets or retrofitted in an existing standard cabinet.
- The Self-Trimming® design requires only a simple rough cut, overlapping the cabinet face for beautiful results
- Includes installation hardware



Sustainability



Available Colors/Finishes

Color tiles intended for reference only.

 NA Stainless Steel



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
6-29-2026 15:46 - US-CA

THE BOLD LOOK
OF **KOHLER**®

Codes/Standards

ASME A112.19.3/CSA B45.4

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-3/4" (94 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Single Bowl
Basin Length:	30-1/4" (768 mm)
Basin Width:	16-9/16" (420 mm)
Basin Depth:	9-3/16" (233 mm)

Material

- Premium 18-gauge stainless steel
-

Recommended Products/Accessories


- K-23726 Drain treatment
 - K-23729 Stainless steel cleaner
 - K-8801 Sink drain and strainer with tailpiece
 - K-8799 Sink drain and strainer basket, less tailpiece
 - K-11352 Disposal flange with stopper
-

Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





Installation

- Undermount

Installation Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the current product template available at www.kohler.com, or by calling 1-800-4KOHLER. Kohler Co. is not responsible for cutout errors when the incorrect cutout template is used.

