



Toccata® | K-RH3346-4

33" top-mount double-bowl kitchen sink

Features

- 36" minimum base cabinet width
- Double-equal bowls
- 8" (203 mm) depth
- Includes installation hardware
- Three faucet holes and one accessory hole to the right



Sustainability



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-03-2026 05:23 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.3/CSA B45.4

Technical Information

All product dimensions are nominal.

Number of Deck Holes:	4
Faucet Hole(s) Size:	1-7/16" (37 mm)
Center(s):	8" (203 mm)
Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Equal Bowls
Left Basin Length:	14-3/16" (360 mm)
Left Basin Width:	15-3/4" (400 mm)
Left Basin Depth:	8" (203 mm)
Right Basin Length:	14-1/8" (359 mm)
Right Basin Width:	15-11/16" (400 mm)
Right Basin Depth:	8" (203 mm)
Cutout:	Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1/2" (13 mm) radius corners

Material

- Premium 19-gauge stainless steel

Recommended Products/Accessories


- K-23726 Drain treatment
- K-23729 Stainless steel cleaner
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket, less tailpiece
- K-6401 Sink rack
- K-3294 Hardwood cutting board, for Undertone®, Cadence®, Iron/Tones®, and Toccata® kitchen sinks
- 1177161 Installation Clip Kit
- K-11352 Disposal flange with stopper

Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





Installation

- Top-mount

Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-03-2026 05:23 - US-CA

THE BOLD LOOK
OF **KOHLER**®