

#### Features

- Insight™ adaptive infrared technology
- 0.5 gpm (1.9 lpm) maximum flow rate
- Factory-set 30-second maximum continual run cycle
- Vandal-resistant aerator
- 8-3/16" (208 mm) spout reach
- Less drain

#### Material

- Brass

#### Installation

- Trim Package only- Requires valve

#### Recommended Products/Accessories

- K-23726 Drain treatment
- K-23723 Faucet cleaner

#### Optional Products/Accessories

- 1160593 .35 gpm Aerator, Small



ADA

CSA B651

OBC

#### Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1


CSA B651

OBC

IAPMO Certification

#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: No

#### Spout:

Spout reach:  $13/16''$  (21 mm)

#### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

### Notes

Install this product according to the installation guide.

The sensor roughing-in allows for installation to a back splash or thicker finished wall than the spout roughing-in.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.