

## Features

- For use with valves with a diverter
- Complements Pinstripe faucets and accessories
- Grooved lever handle and spout
- Requires a Rite-Temp® pressure-balancing valve
- 6-7/8" (175 mm) nondiverter spout with 1/2" NPT connection

## Material

- Premium material construction for durability and reliability

## Installation

- Wall-mount

## Required Products/Accessories

K-11748 Series Rite-Temp® Valves




## Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

## Notes

Install this product according to the installation guide.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Cap the shower outlet if deck-mount spout, diverter, or handshower is connected to the spout outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between the valve and wall-mount spout.