

Features

- Single-handle
- Lever handle
- Stationary spout
- Less drain
- Requires single-handle ceramic valve [K-307-K]
- Available with an 8-1/4" (210 mm) spout from wall to center of drain
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Brass
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount

Recommended Products/Accessories

K-23726 Drain treatment

Optional Products/Accessories

K-7114 Pop-Up Drain
K-7127 Drain
K-7129 Drain
K-33151 Clicker drain without overflow



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Faucet flow rate: 1.2 gal/min (4.5 l/min)

Spout reach: 8-1/4" (210 mm)

Install this product according to the installation guide.

Install the wall-mount valve according to the valve installation guide.

One 1-7/8" (48 mm) diameter cutout hole is required for the spout. One 1-7/8" (48 mm) diameter cutout hole is required for the handle.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.