

KOHLER® Faucets Rite-Temp® bath and shower trim kit with push-button diverter, 1.5 gpm Buckley™ K-T35944-4H

Features

- Single-function 1.5 gpm (5.7 lpm) showerhead
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- A single handle controls both on/off activation and temperature setting
- 6-3/8" (162 mm) non-diverter bath spout with slip-fit connection
- Box includes: Showerhead, faceplate with lever handle and diverter, shower arm with flange, bath spout
- Requires valve (sold separately)
- Coordinates with other products in the Buckley collection
- This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

Material

- Premium material construction with metal handle ensures reliability and durability
- KOHLER finishes resist corrosion and tarnishing

Required Products/Accessories

For wall-mount installation

K-11748 Series Rite-Temp® Valves

Included Components

K-35936 Wall-mount bath spout

K-35948-H Single-function showerhead, 1.5 gpm

K-T35942-4 Rite-Temp® valve trim with diverter



Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

1-15-2026 14:30 - US/CA

THE BOLD LOOK
OF **KOHLER**®



Technical Information

All product dimensions are nominal.

Spout:

- Spout reach: 6-3/8" (163 mm)
- Handshower rated max flow: 1.5 gal/min (5.7 l/min)
- Shower/Rainhead rated max flow: 1.5 gal/min (5.7 l/min)

Shower Valve:

- Flow Rate (Max) @ 45 psi: 1.5 gal/min (5.7 l/min)
- Manufacturer's minimum rated flow: 1.3 gal/min (4.9 l/min)
- Pressure: 45 psi (3.1 bar)
- Maximum (Static) Pressure: 125 psi (8.6 bar)
- Minimum (Operating) Pressure: 20 psi (1.4 bar)

Notes

- Install this product according to the installation guide.
- For use with showerheads or handsprays rated at 1.3 gal/min (4.9 l/min) or higher.
- Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between the valve and the wall-mount spout.