

Features

- Two-handle bathroom faucet trim for wall-mount installations
- Two Lever handles offer separate control of hot and cold water
- 5-5/16" (135 mm) spout reach
- 2.0 gpm (7.6 lpm) maximum flow rate at 60 psi (4.14 bar)
- Simplified form and detail embody the pared-down approach of Stillness, which is as much artistic as it is functional
- Fluid design lines for ease of cleaning
- Coordinate with Stillness faucets, accessories, and showering components to complete your bathroom
- Two-handle bathroom faucet trim, requires valve to complete installation
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Solid-brass construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount

Required Products/Accessories

K-410-K Wall-mount Valve

Recommended Products/Accessories

K-23726 Drain treatment

Optional Products/Accessories

K-7107 Decorative Drain
K-7108 Decorative Drain
K-7129 Drain
K-7129-A Bathroom sink grid drain with overflow
K-8801 Sink drain and strainer with tailpiece
1008176 Handle Kit - Deep Rough-In
K-33151 Clicker drain without overflow
K-25322 Clicker drain with overflow



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
ADA
ICC/ANSI A117.1
CSA B651
OBC

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Faucet flow rate: 2.2 gal/min (8.3 l/min)

Spout reach: 5-5/16" (135 mm)

Install this product according to the installation guide.

Three 1-1/2" (38 mm) diameter cutout holes are required for the spout and handles.

Maintain a minimum distance of 4" (102 mm) minimum between the bottom of spout and the top of fixture rim.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.