

SPECIFICATION FOR LEAP K VERSION				
Flush Volume		Eco Flush 3L Full Flush 4.5L		
Rough in distance		305mm		
Inlet water pressure		Min Inlet Water Pressure 0.07MPa (Dynamic) Max inlet Water Pressure 0.74MPa		
Rated voltage		220-240V~, 50-60Hz		
Rated power		1200W		
Length of power cord		Total Length 1.5m, around 1.2m outside of toilet		
Product dimension		About 680mm x 368.7mm x 491mm		
Product weight		About 43KG		
Inlet water temperature		1-40°C		
Environmental temperature		1-40°C		
Clean	Rear wash		Yes,adjustable	
	Front wash		Yes,adjustable	
	Water flow (water pressure 0.2Mp)		No less than 500mL/min at rear wash	
	Clean water temperature		Off,low,mid,high adjustable/auto(when auto temp active)	
	Clean time(Max)		About 300s	
	Nozzle position adjustment		3 dials	
	Pulsate massage		ON/OFF	
	Oscillate		ON/OFF	
	Safety device	Water overtemp protection		Thermal fuse
Back flow proof		Check valve		
Comfort	Seat temp preservation	Temp adjustment		Off,low,mid,high adjustable/auto(when auto temp active)
		Safety device		Thermal fuse
	Cover		Auto OPEN/CLOSE, slow swing, remote OPEN/CLOSE	
	Seat		Slow swing, remote OPEN/CLOSE	
	Dryer	Dryer function		Yes
		Safety device		Thermal fuse
	Deodorizer function		Yes	
Remote		Yes, function setting refers to Homeowners Guide		
Sanitation	Nozzle self-clean		Yes	
	Antibacterial material		Seat/Cover/Body	
	UV sanitizing		Yes	
Other function	Auxiliary buttonboard		Yes	
	Seating detection		Located inside the seat	
	Auto cover OPEN/CLOSE		Microwave sensing	
	Emergency flush		Yes	
* Power value testing condition: dynamic pressure 0.2Mpa, inlet water temp 15 °C .				