

## M Series Reserve Cabinet MR1648D6 Cabinet Specification Sheet

### FEATURES

- Modular Cabinet - combine multiple cabinets, lighting, or mirrors
- All E0 & E2 cabinets are non-handed/reversible
- Mirrored interior with four adjustable, cantilevered glass shelves
- Cantilever shelving adjustable in 1" increments
- Includes installation hardware for recess mounting
- Includes HT-MAGORG and HT-STORAGETRAY

### ELECTRICAL FEATURES - E2 & E4 MODELS

- Standard knock out for 1/2" (13mm) cable connector
- Wired Internally - Front access serviceability
- USB charging outlet - USB-C & USB-A
- Automatic interior LED Light
- E4 cabinets include Door Defogger and Night Light
- Includes Wire Organizer (VT-WIREORG), Organization Kit (HT-ORGKIT), and Sliding Pull-Out Mag Mirror (VT-SPOMM)

### CONSTRUCTION

- Blum 155° slow close hinges
- Rust free Satin anodized aluminum construction
- 3 mirror design - rear of cabinet and both sides of door
- Safeseal® Gasket with sealed corners on cabinet body

### CODES & STANDARDS

Electric Option Models are ETL certified to:

- UL 962
- CSA Standard C22.2 No. 68

### DIMENSIONS

- Width: 15-1/4" (387 mm)
- Height: 48" (1219 mm)
- Depth: 6-5/8" (169 mm) When surface mounted  
15/16" (23 mm) When recessed  
2-15/16" (74 mm) When semi-recessed

### MORE INFORMATION



Scan the QR code to see the rough opening and electrical details found in the M Series Reserve cabinet installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

### MODEL NUMBER KEY

PRODUCT LINE	WIDTH	HEIGHT	DEPTH	MIRROR OPTIONS	ELECTRIC OPTIONS	HINGE SIDE (E4 ONLY)
MR	16	48	D6	FP = Polished Edge FB = 3/4" Bevel	E0 = Non-Electric E2 = Electric and Interior Light E4 = Electric, Interior Light, Defogger, and Night Light	L = Left R = Right



#### Included with E0




HT-MAGORG HT-STORAGETRAY



VT-SPOMM

#### Included with E2 / E4



HT-ORGKIT



VT-WIREORG



HT-MAGORG

**OPTIONS**

- Plain or Beveled front mirror
- Other widths / heights / depths available
- Handle Kit: Edgepull-84
- IQ™ Digital Lock Box: DLB, DLB-16 (E0)
- Assorted glass bins:
  - Small (GLASSBIN3.25)
  - Medium (GLASSBIN5.25)
  - Large (GLASSBIN8.5)
- Push-to-open Kit: MPUSHKIT (E0), VT-PUSHKIT (E2 & E4)
- Storage accessories supplied with cabinet also available separately: HT-MAGORG, HT-ORGKIT, HT-STORAGETRAY, VT-WIREORG, VT-SPOMM

**INSTALLATION OPTIONS**

- Compatible Mounting Kits (Single Cabinet):
  - Surface Mount Kit (P2SMKIT48D6P)
  - Semi-Recess Mount Kit (P2SMKIT48D5SRP)
- Pairs with Modular mirrors
- Gangs to M-Series Reserve Cabinet via:
  - Surface Mount Ganging Kit (P2SM-GKIT48D6P)
  - Recessed Ganging Kit (P2RMGKIT)
  - Semi-Recessed Ganging Kit (P2SM-GKIT48D6SRP)
- Gangs to Lighting\* - Reference Ganging kit for the particular light option when ordering.
- Compatible with Vesper, InLine, Profiles, M Series\*, PL Series\*, PL Portray, AiO Cabinet\*, and Vitality Cabinet\*
- Cabinets marked with \* are only compatible when Recess Mounted
- Recessed & Semi-Recessed Mount Rough Opening: 14-1/2" W x 47-1/4" H (368 mm W x 1201 mm H)

