

Features

- 4 frame profiles in 7 finishes
- Quiet close Safeseal® Gasket
- Mirrored interior with 4 adjustable glass shelves
- Non-electric cabinets can be installed with left or right opening
- Includes installation hardware for recess mounting
- Can be recessed or surface mounted (kit required)

Construction

- Satin anodized aluminum body
- 3 mirror design - rear of cabinet and both sides of door
- Blum 130° self-closing hinges
- Safeseal® Gasket with sealed corners on cabinet body
- Adjustable shelving at 2" (51 mm) increments
- Electric Option Cabinet:
 - Standard knock out for 1/2" (13 mm) cable connector
 - Wired internally - Front access serviceability

Codes/Standards Applicable

- Electric Option Models are ETL certified to:
 - UL 962
 - CSA Standard C22.2 No. 68

Dimensions

Height: 39-1/2" (1003 mm)
Width: 19-3/8" (492 mm)
Maximum Depth: 5-1/8" (130 mm) Surface, 1-3/8" (35 mm) Project from wall when recessed


Options

- Left or Right hand hinged
- Electric option
- Other widths / heights / depths available
- All Main Line Framed Cabinets can be paired with Main Line Sconces - Reference when ordering DLFML## or Decorative Glass Sconces - Reference when ordering DLFDG####


Installation Options

Recessed Mount - Rough Opening - 38-5/8" H x 18-1/2" W x 4" D (981 mm H x 470 mm W x 102 mm D)


Surface Mount - Reference Surface Mount Kit when ordering
 MSMK40D4B - Beveled Mirror Kit
 MSMK40D4P - Plain Mirror Kit
 MSMK40D4## - Decorative Kit




(Merion Option Shown)




Rosemont



Bryn Mawr



Merion



Penn Valley

See page 2 for frame dimensions.

Model Number Key

Decorative	Cabinet	Width	Height	Depth	Frame Style	Interior Color	Hinge Side and Electric Option	Finish/Color
D	C	20"	40"	D4	RM = Rosemont BM = Bryn Mawr PV = Penn Valley ME = Merion	G = Classic Gray	Blank = Left/Right Non Electric LE = Left with Electric RE = Right with Electric	70 = Satin Nickel 71 = Brushed Nickel 74 = Brushed Black 75 = Brushed Bronze 76 = Chrome 77 = Polished Nickel 79 = White

Optional Electrical System

- Includes one 15A 110VAC (2 plugs)
- Field wire location as shown in drawing
- 1/2" conduit (Ø 7/8" actual) electrical knockout location shown below

Optional Accessories

- Safety Lock Box - SLB
- Glass Bins
- Pull-out Magnifying Mirror - POMM
- Swing out Magnifying Mirror - SOMM
- Push-to-open Kit

Dimensions projected from wall

		Recessed Mount			
		Bryn Mawr	Rosemont	Merion	Penn Valley
A=		1-3/8" (35 mm)	1-3/8" (35 mm)	1-1/16" (27 mm)	1-1/8" (29 mm)
		1-3/8" (35 mm)	1-3/8" (35 mm)	1-1/16" (27 mm)	1-1/8" (29 mm)
B=		1-3/8" (35 mm)	1-3/8" (35 mm)	1-1/16" (27 mm)	1-1/8" (29 mm)
		1-3/8" (35 mm)	1-3/8" (35 mm)	1-1/16" (27 mm)	1-1/8" (29 mm)
		Surface Mount			
		Bryn Mawr	Rosemont	Merion	Penn Valley
B=		4-7/8" (124 mm)	5-1/8" (130 mm)	4-13/16" (122 mm)	4-7/8" (124 mm)

