

Murray Hill Series Facet Frame Cabinet D2C2441MF Specification Sheet

FEATURES

- Hand welded, stainless steel frame with mirrored inlay
- Included push-to-open mechanism for easy access
- All cabinets are non-handed/reversible
- Mirrored interior with 3 adjustable, cantilevered glass shelves
- Cantilever shelving adjustable in 1" increments
- Includes installation hardware for recess mounting
- Recessed mounting only
- Blum 110° slow-close hinges

MATERIALS & CONSTRUCTION

- Rust free Satin anodized aluminum cabinet construction
- Blum hinges standard
- 3 mirror design - rear of cabinet and both sides of door

CODES & STANDARDS


- The Electric Module Option is certified by ETL to:
 - UL 1598
 - CSA C22.2#250.0

OPTIONS

- PORTRAY Electric Upgrade (P2ELECTRIC - included with TP option)
- PORTRAY Quick Caddy (QUICKCADDY - included with TP option)
- IQ™ digital lock box (DLB or DLB-20)
- Solid Stainless Steel handle (EDGE PULL-84)
- Glass Storage Bins (GLASSBIN3.25, GLASSBIN5.25, GLASSBIN8.5)

DIMENSIONS

- Width: 24" (610mm)
- Height: 40-3/4" (1036mm)
- Depth: 1-1/2" (38mm) Exposed frame depth
3-3/16" (81mm) Recessed cabinet depth



MODEL NUMBER KEY

	Width	Height	Frame Style	Frame Finish	Package Option
D2C	24	41	MF = Murray Hill	76 = Chrome 83=Matte Black	SP = Slow-Close Hinges, Push-to-Open Kit TP = Slow-Close Hinges, Push-to-Open Kit, Sliding Magnification Mirror, Quick Caddy, Magnetic Strip, Interior Lighting, USB Charging Ports, Electrical Outlets, Phone Holder

INSTALLATION

Recessed Mount - Rough Opening - 19" W x 35-3/4" H x 4" D (483 mm W x 908 mm H x 102 mm D)

OPTIONAL ELECTRICAL SYSTEM

- 120 VAC 60HZ 20A
- 1/2" conduit (Ø7/8" actual) electrical knockout location

MORE INFORMATION



Scan the QR code to see the rough opening and electrical details found in the Murray Hill Cabinet installation instructions.

Use the camera app on your mobile device to look at this QR code. This will allow you to quickly access web pages and other relevant documents.

