

KALLISTA®

KALLISTA
Pressure Balance Rough-In
P19310-00

Features

- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/resources#ReadyToShip for the complete list of Ready-to-Ship products and finishes
- Brass valve bodies
- One-piece diaphragm cartridge design for ease of maintenance
- High-temperature limit setting for added safety

Recommended Products/Accessories

P24415-CR Pressure balance trim, cross handle
P25018-LV Script Pressure Balance Trim, Lever Handle
P24918-LV Pressure Balance Trim, Lever Handle




Codes/Standards

ASME A112.18.1/CSA B125.1
ASSE 1016

See website for detailed warranty information.

KALLISTA

KALLISTA Pressure Balance Rough-In P19310-00



Technical Information

All product dimensions are nominal.

Notes

All dimensions are nominal.

Install this product according to the installation guide.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Cap the shower outlet if deck-mount spout, diverter, or handshower is connected to the spout outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between the valve and wall-mount spout.

For finished walls greater than 3/4" (19 mm) and less than 1-1/2" (38 mm), install support(s) 2" (51 mm) from the stud face.

For finished walls greater than 1-1/2" (38 mm), install support(s) 3" (76 mm) from the face of the finished wall.