

# KALLISTA®

## KALLISTA Showerhead with Arm P21500-00

### Features

- High-quality solid-brass construction for durability and reliability
- Three spray options available with a simple turn (wide coverage spray, rhythmic pulse spray, and soft aerated spray)
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Wall-mount installation

### Recommended Products/Accessories

P21425-MB Traditional handshower with hose  
P24299-00 Traditional Slidebar with Cross Handle  
P22076-H Body Spray  
P21510-G Air-Induction ECO Small Traditional Rain Showerhead



### Codes/Standards


ASME A112.18.1/CSA B125.1

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.


### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome

# KALLISTA

KALLISTA  
Showerhead with Arm  
P21500-00



## Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

## Notes

For use with automatic compensating valves rated at 1.75 gal/min (6.6 l/min) or less.

Install this product according to the installation instructions.