

Features

- Ready-to-Ship (RTS) Program, in-stock and ready for immediate shipment: Nickel Silver (AD), Brushed Bronze (BV)
- High-quality solid brass construction for durability and reliability
- Required shower arm sold separately
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Single function spray
- Includes escutcheon
- Diameter is 12-7/16" (316 mm)
- Unlacquered Brass (ULB) available in North America and the United Kingdom only

Required Products/Accessories

P21520-00

or

P21521-00

or

P21522-00 Rain Showerhead Arm

or

P21523-00


Recommended Products/Accessories

P31487-PL

P24624-00

P24653-00

P24622-LV



Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992


KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome
	AG	Brushed Nickel
	W6	Weathered Bronze
	ULB	Unlacquered Brass
	SN	Polished Nickel
	BAF	Brushed French Gold
	BV	



Technical Information

All product dimensions are nominal.

Drain included: No

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 2.5 gal/min (9.5 l/min) or less.