KALLISTA.

Foundations by KALLISTA

Air-Induction ECO Small Contemporary Rain Showerhead

P21512-G

Features

- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/ resources#ReadyToShip for the complete list of Readyto-Ship products and finishes
- High-quality solid-brass construction for durability and reliability
- Required shower arm sold separately
- 1.75 gpm (6.6 lpm) maximum flow rate
- Single-function spray
- Includes escutcheon
- Diameter is 8-1/2" (216 mm)

Required Products/Accessories

P21520-00 Rain Showerhead Arm

-

P21521-00 Rain Showerhead Arm

or

P21522-00 12" ceiling-mount rain showerhead arm

or

P21523-00 Wall-Mount Rain Showerhead Arm

Recommended Products/Accessories

P34402-00 Towel Bar, 18"

P21834-00 Wall-mount bath spout

P24843-00 Wand Dual-Function Handshower with Hose

P24421-LV Thermostatic trim, lever handle





Codes/Standards
ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense.
California Energy Commission (CEC)

KALLISTA. Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes Color tiles intended for reference only.


Color	Code	Description
	СР	Polished Chrome
	GN	Gunmetal
	BL	Matte Black
	ULB	Unlacquered Brass
	AF	French Gold
	BAF	Brushed French Gold
	BGP	Brushed Graphite
	BN	Brushed Nickel
	PGP	Polished Graphite
	SN	Polished Nickel
	2MB	Brushed Moderne Brass
	R\/	Rrichad Bronza

KALLISTA.

Foundations by KALLISTA Air-Induction ECO Small Contemporary Rain

Showerhead





Technical Information All product dimensions are nominal.

Shower/Rainhead rated max flow:

1.75 gal/min (6.6 l/min)

Notes Install this product according to the installation instructions.