

Features

- High-quality solid-brass construction for durability and reliability
- Required shower arm sold separately
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Single-function spray
- Includes escutcheon
- Diameter is 8-3/4" (222 mm)

Required Products/Accessories

P21520-00 Rain Showerhead Arm

or

P21521-00 Rain Showerhead Arm

or

P21522-00 12" ceiling-mount rain showerhead arm

or

P21523-00 Wall-Mount Rain Showerhead Arm

or

P21441-00 Rain Showerhead Arm

Recommended Products/Accessories

P31003-PL Shower Door Handle Pull, 6"

P22727-00 Bath Spout

P21425-MB Traditional handshower with hose

P22762-LV Thermostatic Trim, Lever Handle



Codes/Standards

None Applicable

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome

KALLISTA®

For Town by KALLISTA Air-Induction Rain Showerhead P21540-00

Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max 2.5 gal/min (9.5 l/min)
flow:

Notes

For use with automatic compensating
valves rated at 2.5 gal/min (9.5 l/min) or
less.