

Features

- High-quality solid-brass construction for durability and reliability
- Required shower arm sold separately
- 1.75 gpm (6.6 lpm) maximum flow rate
- Single-function spray
- Includes escutcheon
- Diameter is 8-3/4" (222 mm)

Required Products/Accessories

- P21520-00 Rain Showerhead Arm
or
P21521-00 Rain Showerhead Arm
or
P21522-00 12" ceiling-mount rain showerhead arm
or
P21523-00 Wall-Mount Rain Showerhead Arm
or
P21441-00 Rain Showerhead Arm

Recommended Products/Accessories

- P31003-PL Shower Door Handle Pull, 6"
P22727-00 Bath Spout
P21650-00 Traditional Multi-Function Handshower with Hose
P22762-XX Thermostatic Trim, Cross Handle



Codes/Standards

None Applicable

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome

KALLISTA®

For Town by KALLISTA Air-Induction ECO Rain Showerhead P21540-G

Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.75 gal/min (6.6 l/min) or less.