

KALLISTA®

KALLISTA
Traditional Multi-Function Handshower with Hose
P21650-00

Features

- Three spray options available with a simple turn (wide coverage spray, rhythmic pulse spray, and soft aerated spray)
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Includes 59" (1499 mm) hose
- Handshower mounts to deck or wall with your choice of required installation mounting hardware (sold separately)

Recommended Products/Accessories

P21651-00 Wall Bracket with Integrated Supply Elbow
P21653-00 Handshower Trim
P21500-00 Showerhead with Arm
P31003-TT Shower Door Towel Bar, 18"



Codes/Standards

ASME A112.18.1/CSA B125.1
EPA WaterSense®
ICC/ANSI A117.1

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

1-26-2026 20:34 - US

KALLISTA

KALLISTA
Traditional Multi-Function Handshower with Hose
P21650-00



Technical Information

All product dimensions are nominal.

Handshower rated max flow: 1.75 gal/min (6.6 l/min)

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

1-26-2026 20:34 - US