

Features

- High-quality solid-brass construction for durability and reliability
- Required shower arm sold separately
- 1.75 gpm (6.6 lpm) maximum flow rate
- Single-function spray
- Includes escutcheon
- Diameter is 10-1/4" (260 mm)

Required Products/Accessories

P21520-00 Rain Showerhead Arm

or

P21521-00 Rain Showerhead Arm

or

P21522-00 12" ceiling-mount rain showerhead arm

or

P21523-00 Wall-Mount Rain Showerhead Arm

Recommended Products/Accessories

P24933-CPH Towel Bar, 18"

P24914-CPH Wall-Mount Bath Spout

P25656-00 Transitional Handshower with Hose

P24922-CPH Thermostatic Shower Trim, Lever Handle



Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

EPA WaterSense®












California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|-----------------------|
|  | CP | Polished Chrome |
|  | W7 | Black Nickel |
|  | ULB | Unlacquered Brass |
|  | BAF | Brushed French Gold |
|  | BGP | Brushed Graphite |
|  | BN | Brushed Nickel |
|  | PGP | Polished Graphite |
|  | SN | Polished Nickel |
|  | YG | Matte Gold |
|  | 2MB | Brushed Moderne Brass |
|  | BV | Brushed Bronze |

KALLISTA®

Laura Kirar Air-Induction Transitional Rain Showerhead P21676-00



Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.75 gal/min (6.6 l/min) or less.