

### Features

- High-quality solid-brass construction for durability and reliability
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Sprayhead pivots 25 degrees
- Features an internal volume control for complete shut-off

### Recommended Products/Accessories

P21654-00 Traditional Slidebar  
P24299-00 Traditional Slidebar with Cross Handle  
P21386-00 Showerhead with Arm  
P21250-00 Wall-Mount Bath Spout



### Codes/Standards

ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*



| Color                                                                               | Code | Description         |
|-------------------------------------------------------------------------------------|------|---------------------|
|  | CP   | Polished Chrome     |
|  | ULB  | Unlacquered Brass   |
|  | BAF  | Brushed French Gold |
|  | BV   | Brushed Bronze      |
|  | SN   | Polished Nickel     |

# KALLISTA®

## Foundations by KALLISTA

Body Spray

P22076-H



### Technical Information

All product dimensions are nominal.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

7-4-2025 22:03 - US/CA