KALLISTA

Foundations by KALLISTA
Body Spray
P22078-00

Features
- A selection of products within this collection is in stock and ready to ship. Please visit kallista.com/resources#ReadyToShip for the complete list of Ready-to-Ship products and finishes
- High-quality solid-brass construction for durability and reliability
- Easy-to-clean sprayface resists mineral buildup
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Sprayhead pivots 25 degrees
- Features an internal volume control for complete shut-off

Recommended Products/Accessories
P21664-00 Modern Slidebar
P21501-00 Showerhead with Arm

Codes/Standards
ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
NOM Standards
NOM 008-CONAGUA

KALLISTA® Five-Year Limited Warranty
See website for detailed warranty information.

Available Colors/Finishes
Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	W7	Black Nickel
	ULB	Unlacquered Brass
	AF	French Gold
	BAF	Brushed French Gold
	BGP	Brushed Graphite
	BN	Brushed Nickel
	BV	Brushed Bronze
	PGP	Polished Graphite
	SN	Polished Nickel
	2MB	Brushed Moderne Brass

KALLISTA

Foundations by KALLISTA

Body Spray

P22078-00







Technical Information

All product dimensions are nominal.