

### Features

- A selection of products within this collection is in stock and ready to ship. Please visit [kallista.com/resources#ReadyToShip](http://kallista.com/resources#ReadyToShip) for the complete list of Ready-to-Ship products and finishes
- Easy-to-clean sprayface resists mineral buildup
- Maximum flow rate of 2.5 gpm (9.5 lpm)
- Adjustable pivoting sprayface

### Recommended Products/Accessories

- P21664-00 Modern Slidebar
- P21501-00 Showerhead with Arm
- P24712-00 Air-Induction Showerhead with Arm
- P24704-00 Wall-Mount Bath Spout



### Codes/Standards

- ASME A112.18.1/CSA B125.1
- DOE - Energy Policy Act 1992
- NOM Standards
- NOM 008-CONAGUA



### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	GN	Gunmetal
	BL	Matte Black
	W7	Black Nickel
	ULB	Unlacquered Brass
	AF	French Gold
	BAF	Brushed French Gold
	BGP	Brushed Graphite
	BN	Brushed Nickel
	BV	Brushed Bronze
	PGD	Moderne Polished Gold
	PGP	Polished Graphite
	SN	Polished Nickel
	2MB	Brushed Moderne Brass



### Technical Information

All product dimensions are nominal.