

# KALLISTA.

Bellis® by KALLISTA  
Sink Faucet, Traditional Spout, Cross Handles  
P24600-CR

## Features

- High-quality solid-brass construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- 1.2 gpm (4.5 lpm) maximum flow rate
- Spout reach is 5" (127 mm)
- Includes drain and lift rod
- Laminar flow

## Recommended Products/Accessories

P74231-WO Under-mount Sink, Centric Oval with Overflow

P24601-LV Sink Faucet, Noble Spout, Lever Handles

P34600-00 Towel Bar, 24"

P34606-00 Hook



ADA



## Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

EPA WaterSense®

ADA

ICC/ANSI A117.1

## KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------



AD Nickel Silver



CP Polished Chrome



ULB Unlacquered Brass

---

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

1-26-2026 20:45 - US

# KALLISTA.

Bellis® by KALLISTA  
Sink Faucet, Traditional Spout, Cross Handles  
P24600-CR



## Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Spout:

Spout reach: 5" (127 mm)

## Pressure/fixture Supply Requirements

Min flow rate: 1.2 gpm (4.5 lpm)

## Notes

ADA compliant when installed to the specific requirements of these regulations.