

KALLISTA®

Bellis® by KALLISTA Sink Faucet, Noble Spout, Lever Handles P24601-LV

Features

- High-quality solid-brass construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- 1.2 gpm (4.5 lpm) maximum flow rate
- Spout reach is 5" (127 mm)
- Includes drain and lift rod
- Laminar flow

Recommended Products/Accessories

- P74237-WO Under-mount Sink, Soft Oval with Overflow
- P24600-CR Sink Faucet, Traditional Spout, Cross Handles
- P34610-00 Towel Ring
- P34606-00 Hook



Codes/Standards




- ASME A112.18.1/CSA B125.1
- NSF/ANSI/CAN 61
- EPA WaterSense®
- ADA
- ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome
	ULB	Unlacquered Brass

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

12-27-2025 19:40 - US

KALLISTA

Bellis® by KALLISTA Sink Faucet, Noble Spout, Lever Handles P24601-LV



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Pressure/fixture Supply Requirements

Min flow rate: 1.8 gpm (6.8 lpm)

Notes

ADA compliant when installed to the specific requirements of these regulations.