KALLISTA®

Per Se® Decorative by KALLISTA

Sink faucet, low spout, clear crystal knob handles

P24705-CC

Features

- Extended lead time, please contact KALLISTA customer service (888-452-5547) for availability. Product is not available for commercial specification at this time
- Hand-cut French crystal knobs by Saint-Louis
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-11/16" (144 mm)
- Laminar flow
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate

Recommended Products/Accessories

P74234-WO Under-mount Sink, Soft Rectangle with Overflow, Glazed
P24705-CB Sink faucet, low spout, Black Crystal knob handles
P34701-00 Towel Bar, 18"
P34706-00 Hook

CSA B651 | OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ICC/ANSI A117.1
CSA B651
OBC
NOM Standards
NOM 012-CONAGUA

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	French Gold
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel
	BV	Brushed Bronze

KALLISTA

Per Se® Decorative by KALLISTA

Sink faucet, low spout, clear crystal knob handles

P24705-CC



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.2 gal/min (4.5 l/min)
Drain included:	Yes
Drain with overflow:	Yes

Spout:

Spout reach:	5-11/16" (145 mm)

Pressure/fixture Supply Requirements

Min flow rate:	1.2 gpm (4.5 lpm)

Notes

OBC, CSA B651 compliant when installed to the specific requirements of these regulations.