KALLISTA®

Per Se® Decorative by KALLISTA

Sink faucet, low spout, gold flake crystal handles

P24705-GF

Features

- Extended lead time, please contact KALLISTA customer service (888-452-5547) for availability. Product is not available for commercial specification at this time
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-11/16" (144 mm)
- Laminar flow
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate

Recommended Products/Accessories

P74234-WO Under-mount Sink, Soft Rectangle with Overflow, Glazed
P24736-LV Sink Faucet, Tall Spout, Lever Handles
P34701-00 Towel Bar, 18"
P34706-00 Hook

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ICC/ANSI A117.1
NOM Standards
NOM 012-CONAGUA

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	French Gold
	BAF	Brushed French Gold
	BN	Brushed Nickel
	SN	Polished Nickel
	BV	Brushed Bronze

KALLISTA®

Per Se® Decorative by KALLISTA

Sink faucet, low spout, gold flake crystal handles

P24705-GF



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.2 gal/min (4.5 l/min)
Drain included:	Yes
Drain with overflow:	Yes

Spout:

Spout reach:	5-11/16" (144 mm)

Pressure/fixture Supply Requirements

Min flow rate:	1.2 gpm (4.5 lpm)