

KALLISTA®

Bellis® by KALLISTA Traditional Showerhead with Arm P24871-00

Features

- High-quality solid-brass construction for durability and reliability
- Single-function spray
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Wall-mount installation

Recommended Products/Accessories

P24653-00 Single-function Handshower and Hose with 1.75 GPM
P24615-LV Pressure Balance Trim, Lever Handle
P22076-00 Body Spray
P21510-G Air-Induction ECO Small Traditional Rain Showerhead



Codes/Standards

ASME A112.18.1/CSA B125.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	AD	Nickel Silver
	CP	Polished Chrome
	W6	Weathered Bronze
	24K	Polished Gold
	ULB	Unlacquered Brass
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel
	BAF	Brushed French Gold

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

7-4-2025 01:31 - US

KALLISTA®

Bellis® by KALLISTA
Traditional Showerhead with Arm
P24871-00

Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

For use with automatic compensating valves rated at 1.75 gal/min (6.6 l/min) or less.