

KALLISTA®

Paletta™ by Laura Kirar Wall-Mount Sink Faucet, Lever Handles P24910-CPH

Features

- High-quality solid-brass construction for durability and reliability
- Three-hole installation
- Required rough-in sold separately (P29304-00-NA)
- 1.2 gpm (4.5 lpm) maximum flow rate
- Spout reach is 6-1/8" (156 mm)
- Includes soft-touch drain
- Laminar flow

Required Products/Accessories

P29304-00 Rough-In

Adapters, Rough-in and Extension Kits

P29304-00

Range: 2-1/4" (57 mm) -
3-1/2" (89 mm)

Recommended Products/Accessories

P24901-CPH Sink Faucet, Low Spout, Lever Handles

P25336-CPH Towel ring

P24936-CPH Hook



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

CSA B651

OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



CP	Polished Chrome
----	-----------------

1-888-4-KALLISTA (1-888-452-5547)



Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

7-4-2025 22:13 - US/CA

KALLISTA®

Paletta™ by Laura Kirar Wall-Mount Sink Faucet, Lever Handles P24910-CPH



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Drain with
overflow: Yes

Spout:

Spout reach: 6-1/8" (156 mm)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.