

# KALLISTA®

## Laura Kirar Transitional Showerhead with Arm P24942-00

### Features

- High-quality solid-brass construction for durability and reliability
- Single-function spray
- Easy-to-clean sprayface resists mineral buildup
- 1.75 gpm (6.6 lpm) maximum flow rate
- Wall-mount installation

### Recommended Products/Accessories

P21652-00 Fixed Wall Bracket with Integrated Supply Elbow  
P21486-00  
P21487-00  
P25656-00 Transitional Handshower with Hose  
P24915-CPH Pressure Balance Shower Trim, Lever Handle  
P24918-LV Pressure Balance Trim, Lever Handle  
P21676-00 Air-Induction Transitional Rain Showerhead



### Codes/Standards













ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992  
EPA WaterSense®  
California Energy Commission (CEC)

### KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	BL	Matte Black
	W7	Black Nickel
	ULB	Unlacquered Brass
	BAF	Brushed French Gold
	BGP	Brushed Graphite
	BN	Brushed Nickel
	PGP	Polished Graphite
	YG	Matte Gold
	BV	Brushed Bronze
	2MB	Brushed Moderne Brass
	CN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kallista.com](http://www.kallista.com).

7-4-2025 01:31 - US/CA

# KALLISTA®

Laura Kirar  
Transitional Showerhead with Arm  
P24942-00



## Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

## Notes

For use with automatic compensating valves rated at 1.75 gal/min (6.6 l/min) or less.

Install this product according to the installation instructions.