

KALLISTA.

Quincy™ by KALLISTA
Pull-Down Kitchen Faucet
P25000-00

Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 9-7/8" (251 mm)
- 1.8 gpm (6.8 lpm) maximum flow rate
- Two-hole installation
- Compact three-function sprayhead provides spray, aerated flow, and pause functions at the touch of a button
- Sink strainer with tailpiece sold separately

Recommended Products/Accessories

L20307-00 Stainless Steel Kitchen Sink with Standard

Accessories

P34000-00 Sink strainer

P25001-00 Deck-Mount Bridge Faucet, Lever Handles

P25015-00 Soap/Lotion Dispenser



ADA

Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------


	AD	Nickel Silver
	CP	Polished Chrome
	AG	Brushed Nickel
	ULB	Unlacquered Brass

KALLISTA.

Quincy™ by KALLISTA

Pull-Down Kitchen Faucet

P25000-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.8 gal/min (6.8 l/min)

Spout:

Spout reach: 9-7/8" (251 mm)

Notes

Notes ADA compliant when installed to the specific requirements of these regulations.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

1-26-2026 21:02 - US