

KALLISTA.

Quincy™ by KALLISTA
Deck-Mount Bridge Faucet, Lever Handles
P25001-00

Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 8-9/16" (217 mm)
- 1.8 gpm (6.8 lpm) maximum flow rate
- Two-hole installation
- 360-degree swing spout
- Sink strainer with tailpiece sold separately

Recommended Products/Accessories

P23148-LV Contemporary filter faucet
L20857-00 36" Apron-front Kitchen Sink
P25015-00 Soap/Lotion Dispenser
P34014-00 Air Gap Body With Cover



ADA

Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	AD	Nickel Silver
	CP	Polished Chrome
	AG	Brushed Nickel
	ULB	Unlacquered Brass

KALLISTA.

Quincy™ by KALLISTA
Deck-Mount Bridge Faucet, Lever Handles
P25001-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.75 gal/min (6.6 l/min)

Spout:

Spout reach: 8-9/16" (218 mm)

Notes

ADA compliant when installed to the specific requirements of these regulations.