

KALLISTA®

Script® by KALLISTA Deck-Mount Bath Faucet with Diverter, Cross Handles P25003-CR

Features

- High-quality solid metal construction for durability and reliability
- Widespread bath faucet for 8" (203 mm) - 26" (660 mm) centers
- Required rough-in sold separately (P19304-00-NA)
- Required handshower and handshower trim sold separately
- Spout reach is 7-1/4" (184 mm)

Required Products/Accessories

P24761-00 Handshower with Hose

or

P21653-00 Handshower Trim

or

For deck-mount installation

P19304-00 Deck-Mount Bath Valve with Diverter

Adapters, Rough-in and Extension Kits

P19304-00 Range: 1/4" (6 mm) -
4-1/2" (114 mm)

Recommended Products/Accessories

P50045-00 Large Rectangular Bathtub
P21931-00 Traditional Drain Trim Kit
P25041-00 Towel Bar, 24"
P25006-CR Script Sink Faucet, Low Spout, Cross Handles



CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

EPA WaterSense®

ICC/ANSI A117.1

CSA B651

OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty
information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BAF	Brushed French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel

1-888-4-KALLISTA (1-888-452-5547)


Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-15-2025 21:55 - US/CA

KALLISTA

Script® by KALLISTA
Deck-Mount Bath Faucet with Diverter, Cross
Handles
P25003-CR



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: No

Drain with
overflow: No

Spout:

Spout reach: 7-1/4" (185 mm)

Pressure/fixture Supply Requirements

Min flow rate: 1.2 gpm (4.5 lpm)

Notes

OBC, CSA B651 compliant when installed
to the specific requirements of these
regulations.

1-888-4-KALLISTA (1-888-452-5547)

Kallista reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kallista.com.

2-15-2025 21:55 - US/CA