

KALLISTA.

Quincy™ by KALLISTA
Bar Faucet
P25005-00

Features

- High-quality solid-brass construction for durability and reliability
- Spout reach is 6-7/8" (175 mm)
- 1.8 gpm (6.8 lpm) maximum flow rate
- Two-hole installation
- 4" (102 mm) minimum, 8" (203 mm) maximum distance between spout and handle
- Sink strainer with tailpiece sold separately

Recommended Products/Accessories

L20308-00 18" Bar Sink

P25015-00 Soap/Lotion Dispenser

P34000-00 Sink strainer

P25000-00 Pull-Down Kitchen Faucet



ADA

Codes/Standards

ASME A112.18.1/CSA B125.1

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

ADA

ICC/ANSI A117.1

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



AD Nickel Silver



CP Polished Chrome




AG Brushed Nickel



ULB Unlacquered Brass

KALLISTA.

Quincy™ by KALLISTA
Bar Faucet
P25005-00



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.75 gal/min (6.6 l/min)

Spout:

Spout reach: 6-7/8" (175 mm)

Notes

ADA compliant when installed to the specific requirements of these regulations.