KALLISTA®

Script® Decorative by KALLISTA

Sink faucet, low spout, grey crystal knob handles

P25050-SLG

Features

- Hand-cut French crystal knobs by Saint-Louis
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- Spout reach is 5-1/2" (140 mm)
- Includes drain and lift rod
- 1.2 gpm (4.5 lpm) maximum flow rate
- Aerated flow

Recommended Products/Accessories

P74241-WO Under-mount Sink, Soft Oval with Overflow, Glazed
P25007-LV Sink Faucet, Arch Spout, Lever Handles
P25041-00 Towel Bar, 24"
P25046-00 Hook

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BAF	Brushed French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel
	2MB	Brushed Moderne Brass

KALLISTA

Script® Decorative by KALLISTA

Sink faucet, low spout, grey crystal knob handles

P25050-SLG



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.2 gal/min (4.5 l/min)
Drain included:	Yes
Drain with overflow:	Yes

Spout:

Spout reach:	5-1/2" (140 mm)

Pressure/fixture Supply Requirements

Min flow rate:	1.2 gpm (4.5 lpm)

Notes

Install this product according to the installation instructions.