KALLISTA

Script® Decorative by KALLISTA

Sink faucet, arch spout, Spring Rain lever handles

P25055-SPR

Features

- Handcrafted fired enamel handle insert with Spring Rain pattern
- High-quality solid metal construction for durability and reliability
- Widespread sink faucet for 8" – 16" (203 – 406 mm) centers
- 6-3/16" (157 mm) spout reach
- Aerated flow
- Includes soft-touch drain
- 1.2 gpm (4.5 lpm) maximum flow rate

Recommended Products/Accessories

P74241-WO Under-mount Sink, Soft Oval with Overflow, Glazed
P25011-LV Wall-Mount Sink Faucet, Lever Handles
P25013-00 Towel Ring
P25046-00 Hook

ADA | CSA B651 | OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC

KALLISTA® Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BAF	Brushed French Gold
	BN	Brushed Nickel
	BV	Brushed Bronze
	SN	Polished Nickel
	2MB	Brushed Moderne Brass

KALLISTA

Script® Decorative by KALLISTA

Sink faucet, arch spout, Spring Rain lever handles

P25055-SPR



Technical Information

All product dimensions are nominal.

Faucet flow rate:	1.2 gal/min (4.5 l/min)
Drain included:	Yes
Drain with overflow:	Yes

Spout:

Spout reach:	6-3/16" (157 mm)

Pressure/fixture Supply Requirements

Min flow rate:	1.2 gpm (4.5 lpm)

Notes

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.